



Fotoprzełączniki G6, Fotoprzełącznik odbiciowy, energetyczny

GTE6-P4212



Nazwa modelu > **GTE6-P4212**

Numer części > **1051781**



Produkt może różnić się od ilustracji

At a glance

- PinPoint LED for a bright, precise light spot
- Durable metal threaded inserts
- SICK ASIC technology - the result of decades of experience in photoelectric sensors
- Large, user-friendly potentiometer
- Large, bright indicator LEDs
- IP 67 enclosure rating

Your benefits

- Easy alignment and precise object detection due to a highly visible PinPoint LED
- Quick and easy mounting and high durability due to threaded metal inserts
- SICK ASIC technology provides high performance, excellent reliability and crosstalk immunity
- Easy to adjust due to large, user-friendly potentiometers
- Easy to monitor due to large, bright indicator LEDs
- Easy installation with SICK accessories



Cechy

Zasada działania czujnika/Sposób detekcji:	Fotoprzełącznik odbiciowy, energetyczny
Wymiary (Szer. x Wys. x Głęb.):	12 mm x 31,5 mm x 21 mm
Housing design (light emission):	Prostopadłościenna
Maks. strefa działania:	≤ 300 mm ¹⁾
Sensing range:	≤ 250 mm
Rodzaj światła:	Widzialne światło czerwone
Nadajnik światła:	Pin Point LED ²⁾
Długość fali:	650 nm
Nastawa:	Potencjometr, 5 obrotów
Średnica plamki świetlnej (odległość):	Ø 7 mm (90 mm)

¹⁾ Obiekt odbijający 90% światła (standardowy biały zgodnie z normą DIN 5033) ²⁾ Average service life of 100,000 h at T_A = +25 °C


Mechanika/elektronika

Napięcie zasilania:	10 V DC ... 30 V DC ¹⁾
Pobór prądu:	≤ 30 mA ²⁾
Switching output:	PNP
Tryb przełączania:	Przełączanie jasno/ciemno, wybierane


Switching mode selector:	Selectable via light/dark selector
Napięcie sygnału PNP HIGH/LOW:	VS - (≤ 3 V)/approx. 0 V
Napięcie sygnału NPN HIGH/LOW:	Approx. VS/ ≤ 3 V
Output current I _{max} :	≤ 100 mA ³⁾
Czas reakcji:	$< 1,25$ μ s ⁴⁾
Switching frequency:	500 Hz ⁵⁾
Typ połączenia:	Connector M8, 4-pin
Układ zabezpieczenia:::	A, B, D ⁶⁾ 7) 8)
Ciężar:	20 g
Filtr polaryzacyjny:	-
AS-Interface-Chip:	-
Tworzywo, obudowa:	ABS/PC, Tworzywo sztuczne
Tworzywo, układ optyczny:	PMMA
Rodzaj zabezpieczenia:	IP 67
Dostawa:	Stainless steel mounting bracket (1.4301/304) BEF-W100-A
Ambient operating temperature:	-25 °C ... 55 °C
Ambient storage temperature:	-40 °C ... 70 °C

1) Limit values, operation in short-circuit protected network max. 8 A 2) Bez obciążenia 3) At Vs > 24 V, I_A max = 50 mA 4) Signal transit time with resistive load 5)
 With light/dark ratio 1:1 6) A = V_S connections reverse-polarity protected 7) B = inputs and output reverse-polarity protected 8) D = outputs overcurrent and short-circuit protected

Dimensional drawing




Adjustments possible




- [4] Status indicator LED green: power on
- [5] Status indicator LED,
yellow: Status of received light beam
- [7] Sensitivity adjustment: poti

Connection diagram




Characteristic curve




- |1| Sensing range on grey, 18 % remission
- |2| Sensing range on white, 90 % remission


Connection type



Light spot size



Sensing range diagram



- |1| Scanning distance on black, 18 % remission
- |2| Scanning distance on white, 90 % remission

Australia

Phone +61 3 9457 0600
1800 334 802 – tollfree
E-Mail sales@sick.com.au

Belgium/Luxembourg

Phone +32 (0)2 466 55 66
E-Mail info@sick.be

Brasil

Phone +55 11 3215-4900
E-Mail sac@sick.com.br

Canada

Phone +1 905 771 14 44
E-Mail information@sick.com

Ceská Republika

Phone +420 2 57 91 18 50
E-Mail sick@sick.cz

China

Phone +86 4000 121 000
E-Mail info.china@sick.net.cn
Phone +852-2153 6300
E-Mail ghk@sick.com.hk

Danmark

Phone +45 45 82 64 00
E-Mail sick@sick.dk

Deutschland

Phone +49 211 5301-301
E-Mail kundenservice@sick.de

España

Phone +34 93 480 31 00
E-Mail info@sick.es

France

Phone +33 1 64 62 35 00
E-Mail info@sick.fr

Great Britain

Phone +44 (0)1727 831121
E-Mail info@sick.co.uk

India

Phone +91-22-4033 8333
E-Mail info@sick-india.com

Israel

Phone +972-4-6801000
E-Mail info@sick-sensors.com

Italia

Phone +39 02 27 43 41
E-Mail info@sick.it

Japan

Phone +81 (0)3 3358 1341
E-Mail support@sick.jp

Magyarország

Phone +36 1 371 2680
E-Mail office@sick.hu

Nederlands

Phone +31 (0)30 229 25 44
E-Mail info@sick.nl

Norge

Phone +47 67 81 50 00
E-Mail austefjord@sick.no

Österreich

Phone +43 (0)22 36 62 28 8-0
E-Mail office@sick.at

Polska

Phone +48 22 837 40 50
E-Mail info@sick.pl

România

Phone +40 356 171 120
E-Mail office@sick.ro

Russia

Phone +7-495-775-05-30
E-Mail info@sick.ru

Schweiz

Phone +41 41 619 29 39
E-Mail contact@sick.ch

Singapore

Phone +65 6744 3732
E-Mail admin@sicksgp.com.sg

Slovenija

Phone +386 (0)1-47 69 990
E-Mail office@sick.si

South Africa

Phone +27 11 472 3733
E-Mail info@sickautomation.co.za

South Korea

Phone +82 2 786 6321/4
E-Mail info@sickkorea.net

Suomi

Phone +358-9-25 15 800
E-Mail sick@sick.fi

Sverige

Phone +46 10 110 10 00
E-Mail info@sick.se

Taiwan

Phone +886-2-2375-6288
E-Mail sales@sick.com.tw

Türkiye

Phone +90 (216) 528 50 00
E-Mail info@sick.com.tr

United Arab Emirates

Phone +971 (0) 4 8865 878
E-Mail info@sick.ae

USA/México

Phone +1(952) 941-6780
1 800-325-7425 – tollfree
E-Mail info@sickusa.com

More representatives and agencies
at www.sick.com