



Fotoprzełączniki W4-3 Glass, Fotoprzełącznik refleksyjny

WLG4-3F3234



Nazwa modelu > **WLG4-3F3234**

Numer części > **1028129**



Produkt może różnić się od ilustracji

At a glance

- Fast and reliable setup via teach-in pushbutton
- Continuous threshold adjustment technology to detect objects in changing conditions such as temperature, contamination and reflector wear
- Versions without polarizing filters to better detect depolarizing objects such as PET bottles, CD sleeves and shrink-wrapped, glossy objects

Your benefits

- Reliable and quick setting via the push of a button
- Flat housing design eliminates alignment or mounting brackets, which saves time and money
- Low-cost machine integration due to small dimensions that enable mounting in areas with space restrictions
- Quick and easy setup due to highly visible intensive light spot
- The PinPoint LED's well-defined, intense light spot simplifies alignment
- Nearly all transparent objects can be reliably detected



Cechy

Zasada działania czujnika/Sposób detekcji:	Fotoprzełącznik refleksyjny
Wymiary (Szer. x Wys. x Głęb.):	16 mm x 39,5 mm x 12 mm
Housing design (light emission):	Prostopadłościenna, Flat
Maks. strefa działania:	0,01 m ... 4,5 m ¹⁾
Sensing range:	0,02 m ... 3,5 m ²⁾
Rodzaj światła:	Widzialne światło czerwone
Nadajnik światła:	Pin Point LED ³⁾
Długość fali:	650 nm
Teach-in:	Single teach-in button
Nastawa:	Cable, Teach-in
Średnica plamki świetlnej (odległość):	Ø 75 mm (1,5 m)

1) 2) PL80A ³⁾ Average service life of 100,000 h at T_A = +25 °C


Mechanika/elektronika

Napięcie zasilania:	10 V DC ... 30 V DC ¹⁾
Tętnienia resztkowe:	< 5 Vss ²⁾
Pobór prądu:	≤ 20 mA ³⁾
Wyjście przełączające:	PNP
Tryb przełączania:	Dark-switching

Output current I _{max} ..:	≤ 100 mA
Czas reakcji:	< 0,5 ms ⁴⁾
Switching frequency:	1.000 Hz ⁵⁾
Kąt odbioru:	Ca. 30 °
Tłumienie w drodze optycznej światła:	> 8 %
Sposób przyłączenia:	Cable with connector M8, 4-pin, 100 mm ⁶⁾
Cable material:	PVC
Conductor cross-section:	0,14 mm ²
Cable diameter:	Ø 3,4 mm
Układ zabezpieczenia:::	A, C, D ⁷⁾ ⁸⁾ ⁹⁾
Klasa ochronności:	III
Ciężar:	30 g
Filtr polaryzacyjny:	✓
Tworzywo, obudowa:	ABS, Tworzywo sztuczne
Tworzywo, układ optyczny:	PMMA
Rodzaj zabezpieczenia:	IP 67 IP 66
Emitancja:	Do obiektów transparentnych
Ambient operating temperature:	-40 °C ... 60 °C
Ambient storage temperature:	-40 °C ... 75 °C


¹⁾ Limit values ²⁾ May not exceed or fall short of V_S tolerances ³⁾ Bez obciążenia ⁴⁾ Signal transit time with resistive load ⁵⁾ With light/dark ratio 1:1 ⁶⁾ Do not bend
below 0 °C ⁷⁾ A = V_S connections reverse-polarity protected ⁸⁾ C = interference suppression ⁹⁾ D = outputs overcurrent and short-circuit protected

Dimensional drawing




- [1] Center of optical axis, sender
- [2] Center of optical axis, receiver
- [3] LED indicator orange: status of received light beam
- [4] Status indicator LED green: power on
- [5] Threaded mounting hole M3
- [6] Connection
- [7] Teach-in button

Connection diagram




Characteristic curve



- [1] REF-IRF-56
- [2] PL10F
- [3] PL20A
- [4] PL40A
- [5] PL80A

Sensing range diagram




- |1| REF-IRF-56
- |2| PL10F
- |3| PL20A
- |4| PL40A
- |5| PL80A

■ Sensing range ■ Sensing range typ. max.

- ① REF-IRF-56
- ② PL10F
- ③ PL20A
- ④ PL40A
- ⑤ PL80A

Connection type



Australia

Phone +61 3 9457 0600
1800 334 802 – tollfree
E-Mail sales@sick.com.au

Belgium/Luxembourg

Phone +32 (0)2 466 55 66
E-Mail info@sick.be

Brasil

Phone +55 11 3215-4900
E-Mail sac@sick.com.br

Canada

Phone +1 905 771 14 44
E-Mail information@sick.com

Ceská Republika

Phone +420 2 57 91 18 50
E-Mail sick@sick.cz

China

Phone +86 4000 121 000
E-Mail info.china@sick.net.cn
Phone +852-2153 6300
E-Mail ghk@sick.com.hk

Danmark

Phone +45 45 82 64 00
E-Mail sick@sick.dk

Deutschland

Phone +49 211 5301-301
E-Mail kundenservice@sick.de

España

Phone +34 93 480 31 00
E-Mail info@sick.es

France

Phone +33 1 64 62 35 00
E-Mail info@sick.fr

Great Britain

Phone +44 (0)1727 831121
E-Mail info@sick.co.uk

India

Phone +91-22-4033 8333
E-Mail info@sick-india.com

Israel

Phone +972-4-6801000
E-Mail info@sick-sensors.com

Italia

Phone +39 02 27 43 41
E-Mail info@sick.it

Japan

Phone +81 (0)3 3358 1341
E-Mail support@sick.jp

Magyarország

Phone +36 1 371 2680
E-Mail office@sick.hu

Nederlands

Phone +31 (0)30 229 25 44
E-Mail info@sick.nl

Norge

Phone +47 67 81 50 00
E-Mail austefjord@sick.no

Österreich

Phone +43 (0)22 36 62 28 8-0
E-Mail office@sick.at

Polska

Phone +48 22 837 40 50
E-Mail info@sick.pl

România

Phone +40 356 171 120
E-Mail office@sick.ro

Russia

Phone +7-495-775-05-30
E-Mail info@sick.ru

Schweiz

Phone +41 41 619 29 39
E-Mail contact@sick.ch

Singapore

Phone +65 6744 3732
E-Mail admin@sicksgp.com.sg

Slovenija

Phone +386 (0)1-47 69 990
E-Mail office@sick.si

South Africa

Phone +27 11 472 3733
E-Mail info@sickautomation.co.za

South Korea

Phone +82 2 786 6321/4
E-Mail info@sickkorea.net

Suomi

Phone +358-9-25 15 800
E-Mail sick@sick.fi

Sverige

Phone +46 10 110 10 00
E-Mail info@sick.se

Taiwan

Phone +886-2-2375-6288
E-Mail sales@sick.com.tw

Türkiye

Phone +90 (216) 528 50 00
E-Mail info@sick.com.tr

United Arab Emirates

Phone +971 (0) 4 8865 878
E-Mail info@sick.ae

USA/México

Phone +1(952) 941-6780
1 800-325-7425 – tollfree
E-Mail info@sickusa.com

More representatives and agencies
at www.sick.com