



Fotoprzełączniki W4S-3 Inox Hygiene, Fotoprzełącznik odbiciowy, Tłumienie tła

WTB4S-3N1162H



Nazwa modelu > **WTB4S-3N1162H**

Numer części > **1048095**



Produkt może różnić się od ilustracji

At a glance

- Hygienic designed stainless steel housing and accessories (316L/1.4404)
- Hygienic mounting using M12-adapter thread or D12-adapter shaft
- IP 66, IP 67, IP 68 and IP 69K enclosure rating and Ecolab certified
- Resistant to a variety of common cleaning and disinfection agents
- Best background and extraneous light suppression in its class with OES3 technology and two emitter LED's
- Stainless steel teach-in pushbutton with a metal membrane
- Flexible sensing ranges and hysteresis settings
- Key lock function, remote teach, quality monitoring

Your benefits

- Smooth hygienic housing and accessories with no grooves or crevices eliminates the potential for bacteria to grow, providing a more hygienic solution.
- Long service life in harsh conditions ensures less downtime and fewer replacement costs
- OES3 technology and special optical design ensures reliable detection of objects at an extended range which ensures less machine downtime caused by faulty switching
- Easy adjustment via a stainless steel metal membrane teach-in pushbutton
- Quick and easy format adjustment
- Easy monitoring of sensor status
- Key lock function and parameter download prevent incorrect settings
- Simple sensor cloning



Cechy

Zasada działania czujnika/Sposób detekcji:	Fotoprzełącznik odbiciowy, Tłumienie tła
Wymiary (Szer. x Wys. x Głęb.):	15,25 mm x 49,2 mm x 22,15 mm
Housing design:	Hygiene
Housing design (light emission):	Prostopadłościenna
Maks. strefa działania:	3 mm ... 500 mm ¹⁾
Sensing range:	10 mm ... 350 mm ²⁾
Rodzaj światła:	Widzialne światło czerwone
Nadajnik światła:	Pin Point LED ³⁾
Długość fali:	650 nm
Teach-in:	Single teach-in button
Nastawa:	Teach-in
Średnica plamki świetlnej (odległość):	Ø 6,5 mm (150 mm)


1) 2) Obiekt odbijający 90% światła (standardowy biały zgodnie z normą DIN 5033) 3) Average service life of 100,000 h at T_A = +25 °C

Mechanika/elektronika

Napięcie zasilania:	10 V DC ... 30 V DC ¹⁾
Pobór prądu:	≤ 30 mA ²⁾
Wyjście przełączające:	NPN
Tryb przełączania:	Przełączanie jasno/ciemno, wybierane
Output current I _{max} :	≤ 100 mA
Czas reakcji:	< 0,5 ms ³⁾
Switching frequency:	1.000 Hz ⁴⁾
Sposób przyłączenia:	Cable, 4-wire, 2 m ⁵⁾
Cable material:	PVC
Przekrój przewodu:	0,14 mm ²
Układ zabezpieczenia:::	A B ⁶⁾ 7) 8) C
Klasa ochronności:	III
Ciężar:	80 g
Tworzywo, obudowa:	Stainless steel, Stainless steel 316L
Rodzaj zabezpieczenia:	IP 66 IP 67 IP 68 IP 69K
Ambient operating temperature:	-30 °C ... 60 °C, -30 °C ... 70 °C ⁹⁾
Ambient storage temperature:	-30 °C ... 75 °C
UL File No.:	FDA, UL No. NRKH.E181493 & cUL No. NRKH7.E181493


¹⁾ Limit values, reverse-polarity protected, operation in short-circuit protected network: max. 8 A ²⁾ Bez obciążenia ³⁾ Signal transit time with resistive load ⁴⁾ With light/dark ratio 1:1 ⁵⁾ Do not bend below 0 °C ⁶⁾ A = V_S connections reverse-polarity protected ⁷⁾ B = inputs and output reverse-polarity protected ⁸⁾ C = interference suppression ⁹⁾ At UV ≤ 24 V and IA < 30 mA

Dimensional drawing




- [1] Center of optical axis, receiver
- [2] Center of optical axis, sender
- [3] gasket (tightening torque 6Nm)
- [4] Connector M12
- [5] Status indicator LED,
yellow: Status of received light beam
- [6] Status indicator LED green: power on
- [7] Teach-in button


Connection diagram




Characteristic curve



Connection type



Sensing range diagram



Australia

Phone +61 3 9457 0600
1800 334 802 – tollfree
E-Mail sales@sick.com.au

Belgium/Luxembourg

Phone +32 (0)2 466 55 66
E-Mail info@sick.be

Brasil

Phone +55 11 3215-4900
E-Mail sac@sick.com.br

Canada

Phone +1 905 771 14 44
E-Mail information@sick.com

Česká republika

Phone +420 2 57 91 18 50
E-Mail sick@sick.cz

China

Phone +86 4000 121 000
E-Mail info.china@sick.net.cn
Phone +852-2153 6300
E-Mail ghk@sick.com.hk

Danmark

Phone +45 45 82 64 00
E-Mail sick@sick.dk

Deutschland

Phone +49 211 5301-301
E-Mail info@sick.de

España

Phone +34 93 480 31 00
E-Mail info@sick.es

France

Phone +33 1 64 62 35 00
E-Mail info@sick.fr

Great Britain

Phone +44 (0)1727 831121
E-Mail info@sick.co.uk

India

Phone +91-22-4033 8333
E-Mail info@sick-india.com

Israel

Phone +972-4-6801000
E-Mail info@sick-sensors.com

Italia

Phone +39 02 27 43 41
E-Mail info@sick.it

Japan

Phone +81 (0)3 3358 1341
E-Mail support@sick.jp

Magyarország

Phone +36 1 371 2680
E-Mail office@sick.hu

Nederland

Phone +31 (0)30 229 25 44
E-Mail info@sick.nl

Norge

Phone +47 67 81 50 00
E-Mail austefjord@sick.no

Österreich

Phone +43 (0)22 36 62 28 8-0
E-Mail office@sick.at

Polska

Phone +48 22 837 40 50
E-Mail info@sick.pl

România

Phone +40 356 171 120
E-Mail office@sick.ro

Russia

Phone +7-495-775-05-30
E-Mail info@sick.ru

Schweiz

Phone +41 41 619 29 39
E-Mail contact@sick.ch

Singapore

Phone +65 6744 3732
E-Mail sales.gsg@sick.com

Slovenija

Phone +386 (0)1-47 69 990
E-Mail office@sick.si

South Africa

Phone +27 11 472 3733
E-Mail info@sickautomation.co.za

South Korea

Phone +82 2 786 6321/4
E-Mail info@sickkorea.net

Suomi

Phone +358-9-25 15 800
E-Mail sick@sick.fi

Sverige

Phone +46 10 110 10 00
E-Mail info@sick.se

Taiwan

Phone +886-2-2375-6288
E-Mail sales@sick.com.tw

Türkiye

Phone +90 (216) 528 50 00
E-Mail info@sick.com.tr

United Arab Emirates

Phone +971 (0) 4 8865 878
E-Mail info@sick.ae

USA/México

Phone +1(952) 941-6780
1 800-325-7425 – tollfree
E-Mail info@sickusa.com

More representatives and agencies
at www.sick.com